

Product change notification (PCN)

Title / short description	Inline ... - Elimination of printed packing slips, change of packaging
Affected article category	SPS and I/O systems
Change category	Documentation, Packaging
Change number	CDR230090-00
Reason for PCN/PDN Revision	

Purpose/objective of the change

Environmental protection, packing slips

Detailed description of the change

We strive to avoid generating unnecessary waste, both in terms of packaging and package contents. Therefore, in future, the packing slips of the listed products will only be available digitally, with a QR code printed on the labels. A hardcopy of the packing slip will no longer be included. Mixed deliveries may be shipped during the transition period.

Similarly, from this change onwards, an antistatic coating will no longer be used on the packaging carton. With the introduction of the QR code, the entire page printing will be redesigned. The previous bar code is replaced by a data matrix code, which contains further module information in addition to the serial number. Similarly, from this change onwards, an antistatic coating will no longer be used on the packaging carton. The effective date of the change is in the past because this product change notice affects many items, and the transition cannot be scheduled for a specific date. The first products have been updated since the specified date.

Identifying characteristics

QR code and the increased V/C on the packaging label .

Start of Production (SOP)	-	Last Time Delivery (LTD)	-
Effective date (EOP)	2025-04-01	End of Service (EOSR)	-
End of Sales (EOS)	-		

Short-term change (< 6 months) or discontinuation (< 12 months), due to:

- | | | |
|---|---|--|
| ☐ Software / Firmware Bugfix | ☐ Short-term delivery stop by supplier | ☐ Short-term recall by supplier |
| ☐ Force majeure | ☐ Product improvement with customer benefits | |
| ☐ Others | | |

Attachments

- PCN-CDR230090-future production status.jpg
- Material_list.csv
- PCN-CDR230090-00_EN

Material list

Item no.	Item Type	Hardware old	Firmware new	Item no.	Substitute item Type
2692306	IB IL 24 DI 4-2MBD-PAC	08	09		
2692720	IB IL IFS-MA-PAC	08	09		
2692885	IB IL 24 DI 32/HD-2MBD-PAC	10	11		
2692898	IB IL 24 DO 32/HD-2MBD-PAC	10	11		
2693020	IB IL 24 PWR IN/R/L-0.8A-PAC	10	11		
2700172	IB IL 24 DO8/HD-PAC	11	12		
2700196	IB IL CAN-MA-PAC	06	07		
2700458	IB IL AI 4/I-PAC	09	10		
2700459	IB IL AI 4/U-PAC	08	09		
2701000	IB IL TEMP 8 UTH/RTD-PAC	02	03		
2701009	IB IL 24 DO 4/EF-PAC	04	05		
2701480	IB IL 48 DI8/HD-PAC	02	03		
2702141	IB IL RS 485-ECO	03	04		
2702373	IB IL SGI 2/P/EF-PAC	03	04		
2702502	IB IL UTH 4/J-ECO	03	04		
2702503	IB IL UTH 4/K-ECO	03	04		
2702825	IB IL 24 DO 4/EF-ECO	02	03		
2736903	IB IL 24 FLM-PAC	07	08		
2819574	IB IL SSI-IN-PAC	10	11		
2819765	IB IL INC-IN-2MBD-PAC	09	10		
2861205	IB IL 24 MUX MA-PAC	11	12		
2861221	IB IL 24 DI 2-PAC	09	10		
2861234	IB IL 24 DI 4-PAC	15	16		
2861247	IB IL 24 DI 8-PAC	14	15		
2861250	IB IL 24 DI 16-PAC	13	14		
2861263	IB IL 24 DO 2-2A-PAC	13	14		
2861276	IB IL 24 DO 4-PAC	14	15		
2861289	IB IL 24 DO 8-PAC	14	15		
2861292	IB IL 24 DO 16-PAC	15	16		
2861315	IB IL AO 1/SF-PAC	21	22		
2861328	IB IL TEMP 2 RTD-PAC	12	13		
2861331	IB IL 24 PWR IN-PAC	13	14		
2861344	IB IL 24 SEG-PAC	09	10		
2861357	IB IL RS 232-PAC	07	08		
2861360	IB IL 24 TC-PAC	06	07		
2861373	IB IL 24 SEG/F-PAC	10	11		
2861386	IB IL TEMP 2 UTH-PAC	12	13		
2861399	IB IL AO 1/U/SF-PAC	11	12		

Item no.	Item Type	Hardware old	Firmware new	Item no.	Substitute item Type
2861409	IB IL 24 SEG-ELF-PAC	07	08		
2861438	IB IL 24 PWR IN/F-PAC	07	08		
2861441	IBS IL 24 RB-T-PAC	09	10		
2861467	IB IL AO 2/U/BP-PAC	11	12		
2861603	IB IL 24 DO 8-2A-PAC	08	09		
2861632	IB IL PWM/2-PAC	09	10		
2861687	IB IL 24 DO 8-2MBD-PAC	11	12		
2861690	IB IL 24 DI 8-2MBD-PAC	08	09		
2861700	IB IL 24 DO 2-2A-2MBD-PAC	09	10		
2861852	IB IL CNT-PAC	09	10		
2861904	IB IL 24 SEG/F-D-PAC	09	10		
2861933	IB IL RS 485/422-PAC	08	09		
2861959	IB IL 24 DI16-2MBD-PAC	07	08		
2861962	IBS IL 24 RB-T-2MBD-PAC	08	09		
2861988	IB IL 24 DO 4-2MBD-PAC	07	08		
2862084	IB IL RS 232-2MBD-PAC	07	08		
2862097	IB IL RS 485/422-2MBD-PAC	08	09		
2862152	IB IL 24 PWR IN/2-F-D-PAC	09	10		
2862204	IB IL 24 DI 8/T2-PAC	12	13		
2862822	IB IL 24 DO 32/HD-PAC	15	16		
2862835	IB IL 24 DI 32/HD-PAC	15	16		
2862958	IB IL 24 DI 16-PAC/SN	11	12		
2862987	IB IL PD 24V-PAC	06	07		
2862990	IB IL PD GND-PAC	06	07		
2863119	IB IL 24/48 DOR 2/W-PAC	08	09		
2863520	IB IL 24 DI 16-NPN-PAC	11	12		
2863627	IB IL RS 485/422-PRO-PAC	13	14		
2863834	IB IL 24 PWR IN/2F-DF-2MBD-PAC	04	05		
2863928	IB IL 24 DI 4-ME	10	11		
2863931	IB IL 24 DO 4-ME	09	10		
2863957	IB IL AO 2/U/BP-ME	07	08		
2878036	IB IL AO 4/8/U/BP-PAC	06	07		
2878052	IB IL AO 4/8/U/BP-2MBD-PAC	06	07		
2878159	IBS IL 24 RB-LK-2MBD	03	04		
2878243	IB IL 24 DI 32/HD-NPN-PAC	10	11		
2878340	IB IL 24 DO 32/HD-NPN-PAC	10	11		
2878722	IB IL RS 232-PRO-PAC	12	13		
2897156	IB IL 24 DI 16-ME	04	05		
2897253	IB IL 24 DO 16-ME	07	08		

Item no.	Item Type	Hardware old	Firmware new	Item no.	Substitute item Type
2897402	IB IL TEMP 4/8 RTD/EF-PAC	15	16		
1185434	IB IL RTD 4/NTC-ECO	00	01		
2403696	IL PN BK-PAC	10	11		
2692306	IB IL 24 DI 4-2MBD-PAC	07	08		
2692322	IL PB BK DI8 DO4/EF-PAC	14	15		
2692380	IL S3 BK DI8 DO4 2TX-PAC	21	22		
2692720	IB IL IFS-MA-PAC	07	08		
2692885	IB IL 24 DI 32/HD-2MBD-PAC	09	10		
2692898	IB IL 24 DO 32/HD-2MBD-PAC	09	10		
2693020	IB IL 24 PWR IN/R/L-0.8A-PAC	09	10		
2700172	IB IL 24 DO8/HD-PAC	09	10		
2700173	IB IL 24 DI8/HD-PAC	14	15		
2700196	IB IL CAN-MA-PAC	04	05		
2700458	IB IL AI 4/I-PAC	07	08		
2700459	IB IL AI 4/U-PAC	07	08		
2700775	IB IL AO 2/UI-PAC	06	07		
2700893	IB IL RS UNI-PAC	10	11		
2701000	IB IL TEMP 8 UTH/RTD-PAC	01	02		
2701009	IB IL 24 DO 4/EF-PAC	03	03		
2701025	IB IL RS UNI-2MBD-PAC	06	07		
2701480	IB IL 48 DI8/HD-PAC	01	02		
2702141	IB IL RS 485-ECO	02	03		
2702230	IL CO BK-PAC	08	09		
2702372	IL ETH BK-PAC	04	05		
2702373	IB IL SGI 2/P/EF-PAC	02	03		
2702495	IB IL AI 4/I/4-20-ECO	04	05		
2702496	IB IL AI 4/U/0-10-ECO	04	05		
2702497	IB IL AO 4/I/4-20-ECO	05	06		
2702498	IB IL AO 4/U/0-10-ECO	04	05		
2702499	IB IL RTD 4/PT100-ECO	03	04		
2702501	IB IL RTD 4/PT1000-ECO	03	04		
2702502	IB IL UTH 4/J-ECO	02	03		
2702503	IB IL UTH 4/K-ECO	02	03		
2702507	IL EC BK-PAC	06	07		
2702792	IB IL 24 DI 8/HD-ECO	04	05		
2702793	IB IL 24 DO 8/HD-ECO	01	02		
2702795	IB IL RS 232-ECO	01	02		
2702825	IB IL 24 DO 4/EF-ECO	01	02		
2703981	IL ETH BK DI8 DO4 2TX-PAC	24	25		

Item no.	Item Type	Hardware old	Firmware new	Item no.	Substitute item Type
2703994	IL PN BK DI8 DO4 2TX-PAC	26	27		
2736903	IB IL 24 FLM-PAC	06	07		
2819574	IB IL SSI-IN-PAC	09	10		
2819765	IB IL INC-IN-2MBD-PAC	08	09		
2861205	IB IL 24 MUX MA-PAC	10	11		
2861218	IBS IL 24 BK-LK-PAC	11	12		
2861221	IB IL 24 DI 2-PAC	08	09		
2861234	IB IL 24 DI 4-PAC	14	15		
2861247	IB IL 24 DI 8-PAC	13	14		
2861250	IB IL 24 DI 16-PAC	12	13		
2861263	IB IL 24 DO 2-2A-PAC	12	13		
2861276	IB IL 24 DO 4-PAC	13	14		
2861289	IB IL 24 DO 8-PAC	13	14		
2861292	IB IL 24 DO 16-PAC	14	15		
2861302	IB IL AI 2/SF-PAC	12	13		
2861315	IB IL AO 1/SF-PAC	20	21		
2861328	IB IL TEMP 2 RTD-PAC	11	12		
2861331	IB IL 24 PWR IN-PAC	12	09		
2861344	IB IL 24 SEG-PAC	08	06		
2861357	IB IL RS 232-PAC	05	06		
2861360	IB IL 24 TC-PAC	05	06		
2861373	IB IL 24 SEG/F-PAC	09	10		
2861386	IB IL TEMP 2 UTH-PAC	11	12		
2861399	IB IL AO 1/U/SF-PAC	10	11		
2861409	IB IL 24 SEG-ELF-PAC	06	07		
2861412	IB IL AI 8/SF-PAC	11	12		
2861438	IB IL 24 PWR IN/F-PAC	06	07		
2861441	IBS IL 24 RB-T-PAC	08	09		
2861467	IB IL AO 2/U/BP-PAC	10	11		
2861506	IBS IL 24 BK RB-LK-PAC	07	08		
2861577	IB IL AI 2/SF-230-PAC	04	05		
2861580	IBS IL 24 BK-T/U-PAC	13	14		
2861593	IBS IL 24 BK-DSUB-PAC	11	12		
2861603	IB IL 24 DO 8-2A-PAC	07	08		
2861632	IB IL PWM/2-PAC	07	08		
2861661	IB IL AI 8/IS-PAC	06	07		
2861674	IB IL 24 PWR IN/R-PAC	11	12		
2861687	IB IL 24 DO 8-2MBD-PAC	09	10		
2861690	IB IL 24 DI 8-2MBD-PAC	06	07		

Item no.	Item Type	Hardware old	Firmware new	Item no.	Substitute item Type
2861700	IB IL 24 DO 2-2A-2MBD-PAC	08	09		
2861755	IB IL INC-IN-PAC	11	12		
2861768	IB IL IMPULSE-IN-PAC	07	08		
2861852	IB IL CNT-PAC	08	09		
2861865	IB IL SSI-PAC	05	06		
2861904	IB IL 24 SEG/F-D-PAC	08	09		
2861933	IB IL RS 485/422-PAC	06	07		
2861959	IB IL 24 DI16-2MBD-PAC	06	07		
2861962	IBS IL 24 RB-T-2MBD-PAC	07	08		
2861988	IB IL 24 DO 4-2MBD-PAC	06	07		
2862000	IBS IL 24 BK-T/U-2MBD-PAC	09	10		
2862013	IB IL 24 DO16-2MBD-PAC	06	07		
2862068	IBS IL 24 BK-LK-2MBD-PAC	08	09		
2862084	IB IL RS 232-2MBD-PAC	05	06		
2862097	IB IL RS 485/422-2MBD-PAC	07	08		
2862136	IB IL 24 PWR IN/2-F-PAC	05	06		
2862152	IB IL 24 PWR IN/2-F-D-PAC	08	09		
2862194	IB IL AO 2/SF-2MBD-PAC	07	08		
2862204	IB IL 24 DI 8/T2-PAC	11	12		
2862217	IB IL AI 2/4-20-PAC	05	06		
2862246	IL PB BK DP/V1-PAC	16	17		
2862822	IB IL 24 DO 32/HD-PAC	14	15		
2862835	IB IL 24 DI 32/HD-PAC	14	15		
2862958	IB IL 24 DI 16-PAC/SN	10	11		
2862961	IB IL 24 DO 16-PAC/SN	11	12		
2862987	IB IL PD 24V-PAC	04	05		
2862990	IB IL PD GND-PAC	04	05		
2863083	IB IL AO 2/SF-PAC	08	09		
2863119	IB IL 24/48 DOR 2/W-PAC	05	06		
2863135	IB IL 24 PWR IN/PS-PAC	05	06		
2863520	IB IL 24 DI 16-NPN-PAC	10	11		
2863627	IB IL RS 485/422-PRO-PAC	12	13		
2863834	IB IL 24 PWR IN/2F-DF-2MBD-PAC	03	04		
2863915	IB IL TEMP 4/8 RTD-PAC	08	09		
2863928	IB IL 24 DI 4-ME	09	10		
2863931	IB IL 24 DO 4-ME	08	09		
2863944	IB IL AI 2/SF-ME	07	08		
2863957	IB IL AO 2/U/BP-ME	06	07		
2878036	IB IL AO 4/8/U/BP-PAC	05	06		

Item no.	Item Type	Hardware old	Firmware new	Item no.	Substitute item Type
2878052	IB IL AO 4/8/U/BP-2MBD-PAC	05	06		
2878159	IBS IL 24 RB-LK-2MBD	02	03		
2878243	IB IL 24 DI 32/HD-NPN-PAC	09	10		
2878340	IB IL 24 DO 32/HD-NPN-PAC	09	10		
2878447	IB IL AI 4/EF-PAC	11	12		
2878638	IB IL SGI 2/F-PAC	10	11		
2878641	IB IL AI 4/EF-2MBD-PAC	07	08		
2878696	IL MOD BK DI8 DO4-PAC	22	23		
2878722	IB IL RS 232-PRO-PAC	11	12		
2878735	IB IL SGI 2/F-2MBD-PAC	08	09		
2884622	IB IL TEMP 2 RTD-PAC/10	04	05		
2897046	IB IL CNT-PAC/10	07	07		
2897143	IB IL RS 485/422-PRO-PAC/10	08	08		
2897156	IB IL 24 DI 16-ME	03	04		
2897240	IBS IL 24 BK-LK-PAC/10	07	08		
2897253	IB IL 24 DO 16-ME	05	06		
2897334	IB IL 24 DI 2-PAC/10	04	05		
2897347	IBS IL 24 BK-DSUB-PAC/10	06	07		
2897402	IB IL TEMP 4/8 RTD/EF-PAC	14	15		
2897431	IB IL 24 DI 8/T2-PAC/10	05	06		
2897444	IBS IL 24 RB-T-PAC/10	06	07		
2897457	IB IL 24 LSKIP-PAC	06	07		
2897538	IB IL 24 DO 16-PAC/10	05	06		
2897635	IB IL 24 PWR IN-PAC/10	04	05		
2897732	IB IL 24 SEG-ELF-PAC/10	03	04		
2897758	IL EIP BK DI8 DO4 2TX-PAC	18	19		
2897839	IB IL AI 2/SF-PAC/10	05	06		
2897936	IB IL AO 2/U/BP-PAC/10	04	05		
2897952	IB IL AI/TEMP 4 RTD-PAC	02	03		

Phoenix Contact Art.Nr.;	Phoenix Contact Art.Bez.;	Bemerkung
2692306	;IB IL 24 DI 4-2MBD-PAC;HW/FW alt: 08	HW/FW neu: 09
2692720	;IB IL IFS-MA-PAC;HW/FW alt: 08	HW/FW neu: 09
2692885	;IB IL 24 DI 32/HD-2MBD-PAC;HW/FW alt: 10	HW/FW neu: 11
2692898	;IB IL 24 DO 32/HD-2MBD-PAC;HW/FW alt: 10	HW/FW neu: 11
2693020	;IB IL 24 PWR IN/R/L-0.8A-PAC;HW/FW alt: 10	HW/FW neu: 11
2700172	;IB IL 24 DO8/HD-PAC;HW/FW alt: 11	HW/FW neu: 12
2700196	;IB IL CAN-MA-PAC;HW/FW alt: 06	HW/FW neu: 07
2700458	;IB IL AI 4/I-PAC;HW/FW alt: 09	HW/FW neu: 10
2700459	;IB IL AI 4/U-PAC;HW/FW alt: 08	HW/FW neu: 09
2701000	;IB IL TEMP 8 UTH/RTD-PAC;HW/FW alt: 02	HW/FW neu: 03
2701009	;IB IL 24 DO 4/EF-PAC;HW/FW alt: 04	HW/FW neu: 05
2701480	;IB IL 48 DI8/HD-PAC;HW/FW alt: 02	HW/FW neu: 03
2702141	;IB IL RS 485-ECO;HW/FW alt: 03	HW/FW neu: 04
2702373	;IB IL SGI 2/P/EF-PAC;HW/FW alt: 03	HW/FW neu: 04
2702502	;IB IL UTH 4/J-ECO;HW/FW alt: 03	HW/FW neu: 04
2702503	;IB IL UTH 4/K-ECO;HW/FW alt: 03	HW/FW neu: 04
2702825	;IB IL 24 DO 4/EF-ECO;HW/FW alt: 02	HW/FW neu: 03
2736903	;IB IL 24 FLM-PAC;HW/FW alt: 07	HW/FW neu: 08
2819574	;IB IL SSI-IN-PAC;HW/FW alt: 10	HW/FW neu: 11
2819765	;IB IL INC-IN-2MBD-PAC;HW/FW alt: 09	HW/FW neu: 10
2861205	;IB IL 24 MUX MA-PAC;HW/FW alt: 11	HW/FW neu: 12
2861221	;IB IL 24 DI 2-PAC;HW/FW alt: 09	HW/FW neu: 10
2861234	;IB IL 24 DI 4-PAC;HW/FW alt: 15	HW/FW neu: 16
2861247	;IB IL 24 DI 8-PAC;HW/FW alt: 14	HW/FW neu: 15
2861250	;IB IL 24 DI 16-PAC;HW/FW alt: 13	HW/FW neu: 14
2861263	;IB IL 24 DO 2-2A-PAC;HW/FW alt: 13	HW/FW neu: 14
2861276	;IB IL 24 DO 4-PAC;HW/FW alt: 14	HW/FW neu: 15
2861289	;IB IL 24 DO 8-PAC;HW/FW alt: 14	HW/FW neu: 15
2861292	;IB IL 24 DO 16-PAC;HW/FW alt: 15	HW/FW neu: 16
2861315	;IB IL AO 1/SF-PAC;HW/FW alt: 21	HW/FW neu: 22
2861328	;IB IL TEMP 2 RTD-PAC;HW/FW alt: 12	HW/FW neu: 13
2861331	;IB IL 24 PWR IN-PAC;HW/FW alt: 13	HW/FW neu: 14
2861344	;IB IL 24 SEG-PAC;HW/FW alt: 09	HW/FW neu: 10
2861357	;IB IL RS 232-PAC;HW/FW alt: 07	HW/FW neu: 08
2861360	;IB IL 24 TC-PAC;HW/FW alt: 06	HW/FW neu: 07
2897253	;IB IL 24 DO 16-ME;HW/FW alt: 05	HW/FW neu: 06
2897334	;IB IL 24 DI 2-PAC/10;HW/FW alt: 04	HW/FW neu: 05
2897347	;IBS IL 24 BK-DSUB-PAC/10;HW/FW alt: 06	HW/FW neu: 07
2897402	;IB IL TEMP 4/8 RTD/EF-PAC;HW/FW alt: 14	HW/FW neu: 15
2897431	;IB IL 24 DI 8/T2-PAC/10;HW/FW alt: 05	HW/FW neu: 06
2897444	;IBS IL 24 RB-T-PAC/10;HW/FW alt: 06	HW/FW neu: 07
2897457	;IB IL 24 LSKIP-PAC;HW/FW alt: 06	HW/FW neu: 07
2897538	;IB IL 24 DO 16-PAC/10;HW/FW alt: 05	HW/FW neu: 06
2897635	;IB IL 24 PWR IN-PAC/10;HW/FW alt: 04	HW/FW neu: 05
2897732	;IB IL 24 SEG-ELF-PAC/10;HW/FW alt: 03	HW/FW neu: 04
2897758	;IL EIP BK DI8 DO4 2TX-PAC;HW/FW alt: 18	HW/FW neu: 19
2897839	;IB IL AI 2/SF-PAC/10;HW/FW alt: 05	HW/FW neu: 06

2897936	;IB IL AO 2/U/BP-PAC;10;HW/FW alt: 04	HW/FW neu: 05
2897952	;IB IL AI/TEMP 4 RTD-PAC;HW/FW alt: 02	HW/FW neu: 03
2861373	;IB IL 24 SEG/F-PAC;HW/FW alt: 10	HW/FW neu: 11
2861386	;IB IL TEMP 2 UTH-PAC;HW/FW alt: 12	HW/FW neu: 13
2861399	;IB IL AO 1/U/SF-PAC;HW/FW alt: 11	HW/FW neu: 12
2861409	;IB IL 24 SEG-ELF-PAC;HW/FW alt: 07	HW/FW neu: 08
2861438	;IB IL 24 PWR IN/F-PAC;HW/FW alt: 07	HW/FW neu: 08
2861441	;IBS IL 24 RB-T-PAC;HW/FW alt: 09	HW/FW neu: 10
2861467	;IB IL AO 2/U/BP-PAC;HW/FW alt: 11	HW/FW neu: 12
2861603	;IB IL 24 DO 8-2A-PAC;HW/FW alt: 08	HW/FW neu: 09
2861632	;IB IL PWM/2-PAC;HW/FW alt: 09	HW/FW neu: 10
2861687	;IB IL 24 DO 8-2MBD-PAC;HW/FW alt: 11	HW/FW neu: 12
2861690	;IB IL 24 DI 8-2MBD-PAC;HW/FW alt: 08	HW/FW neu: 09
2861700	;IB IL 24 DO 2-2A-2MBD-PAC;HW/FW alt: 09	HW/FW neu: 10
2861852	;IB IL CNT-PAC;HW/FW alt: 09	HW/FW neu: 10
2861904	;IB IL 24 SEG/F-D-PAC;HW/FW alt: 09	HW/FW neu: 10
2861933	;IB IL RS 485/422-PAC;HW/FW alt: 08	HW/FW neu: 09
2861959	;IB IL 24 DI16-2MBD-PAC;HW/FW alt: 07	HW/FW neu: 08
2861962	;IBS IL 24 RB-T-2MBD-PAC;HW/FW alt: 08	HW/FW neu: 09
2861988	;IB IL 24 DO 4-2MBD-PAC;HW/FW alt: 07	HW/FW neu: 08
2862084	;IB IL RS 232-2MBD-PAC;HW/FW alt: 07	HW/FW neu: 08
2862097	;IB IL RS 485/422-2MBD-PAC;HW/FW alt: 08	HW/FW neu: 09
2862152	;IB IL 24 PWR IN/2-F-D-PAC;HW/FW alt: 09	HW/FW neu: 10
2862204	;IB IL 24 DI 8/T2-PAC;HW/FW alt: 12	HW/FW neu: 13
2862822	;IB IL 24 DO 32/HD-PAC;HW/FW alt: 15	HW/FW neu: 16
2862835	;IB IL 24 DI 32/HD-PAC;HW/FW alt: 15	HW/FW neu: 16
2862958	;IB IL 24 DI 16-PAC/SN;HW/FW alt: 11	HW/FW neu: 12
2862987	;IB IL PD 24V-PAC;HW/FW alt: 06	HW/FW neu: 07
2862990	;IB IL PD GND-PAC;HW/FW alt: 06	HW/FW neu: 07
2863119	;IB IL 24/48 DOR 2/W-PAC;HW/FW alt: 08	HW/FW neu: 09
2863520	;IB IL 24 DI 16-NPN-PAC;HW/FW alt: 11	HW/FW neu: 12
2863627	;IB IL RS 485/422-PRO-PAC;HW/FW alt: 13	HW/FW neu: 14
2863834	;IB IL 24 PWR IN/2F-DF-2MBD-PAC;HW/FW alt: 04	HW/FW neu: 05
2863928	;IB IL 24 DI 4-ME;HW/FW alt: 10	HW/FW neu: 11
2863931	;IB IL 24 DO 4-ME;HW/FW alt: 09	HW/FW neu: 10
2863957	;IB IL AO 2/U/BP-ME;HW/FW alt: 07	HW/FW neu: 08
2878036	;IB IL AO 4/8/U/BP-PAC;HW/FW alt: 06	HW/FW neu: 07
2878052	;IB IL AO 4/8/U/BP-2MBD-PAC;HW/FW alt: 06	HW/FW neu: 07
2878159	;IBS IL 24 RB-LK-2MBD;HW/FW alt: 03	HW/FW neu: 04
2878243	;IB IL 24 DI 32/HD-NPN-PAC;HW/FW alt: 10	HW/FW neu: 11
2878340	;IB IL 24 DO 32/HD-NPN-PAC;HW/FW alt: 10	HW/FW neu: 11
2878722	;IB IL RS 232-PRO-PAC;HW/FW alt: 12	HW/FW neu: 13
2897156	;IB IL 24 DI 16-ME;HW/FW alt: 04	HW/FW neu: 05
2897253	;IB IL 24 DO 16-ME;HW/FW alt: 07	HW/FW neu: 08
2897402	;IB IL TEMP 4/8 RTD/EF-PAC;HW/FW alt: 15	HW/FW neu: 16
1185434	;IB IL RTD 4/NTC-ECO;HW/FW alt: 00	HW/FW neu: 01
2403696	;IL PN BK-PAC;HW/FW alt: 10	HW/FW neu: 11
2692306	;IB IL 24 DI 4-2MBD-PAC;HW/FW alt: 07	HW/FW neu: 08

2692322	;IL PB BK DI8 DO4/EF-PAC;HW/FW alt: 14	HW/FW neu: 15
2692380	;IL S3 BK DI8 DO4 2TX-PAC;HW/FW alt: 21	HW/FW neu: 22
2692720	;IB IL IFS-MA-PAC;HW/FW alt: 07	HW/FW neu: 08
2692885	;IB IL 24 DI 32/HD-2MBD-PAC;HW/FW alt: 09	HW/FW neu: 10
2692898	;IB IL 24 DO 32/HD-2MBD-PAC;HW/FW alt: 09	HW/FW neu: 10
2693020	;IB IL 24 PWR IN/R/L-0.8A-PAC;HW/FW alt: 09	HW/FW neu: 10
2700172	;IB IL 24 DO8/HD-PAC;HW/FW alt: 09	HW/FW neu: 10
2700173	;IB IL 24 DI8/HD-PAC;HW/FW alt: 14	HW/FW neu: 15
2700196	;IB IL CAN-MA-PAC;HW/FW alt: 04	HW/FW neu: 05
2700458	;IB IL AI 4/I-PAC;HW/FW alt: 07	HW/FW neu: 08
2700459	;IB IL AI 4/U-PAC;HW/FW alt: 07	HW/FW neu: 08
2700775	;IB IL AO 2/UI-PAC;HW/FW alt: 06	HW/FW neu: 07
2700893	;IB IL RS UNI-PAC;HW/FW alt: 10	HW/FW neu: 11
2701000	;IB IL TEMP 8 UTH/RTD-PAC;HW/FW alt: 01	HW/FW neu: 02
2701009	;IB IL 24 DO 4/EF-PAC;HW/FW alt: 03	HW/FW neu: 03
2701025	;IB IL RS UNI-2MBD-PAC;HW/FW alt: 06	HW/FW neu: 07
2701480	;IB IL 48 DI8/HD-PAC;HW/FW alt: 01	HW/FW neu: 02
2702141	;IB IL RS 485-ECO;HW/FW alt: 02	HW/FW neu: 03
2702230	;IL CO BK-PAC;HW/FW alt: 08	HW/FW neu: 09
2702372	;IL ETH BK-PAC;HW/FW alt: 04	HW/FW neu: 05
2702373	;IB IL SGI 2/P/EF-PAC;HW/FW alt: 02	HW/FW neu: 03
2702495	;IB IL AI 4/I/4-20-ECO;HW/FW alt: 04	HW/FW neu: 05
2702496	;IB IL AI 4/U/0-10-ECO;HW/FW alt: 04	HW/FW neu: 05
2702497	;IB IL AO 4/I/4-20-ECO;HW/FW alt: 05	HW/FW neu: 06
2702498	;IB IL AO 4/U/0-10-ECO;HW/FW alt: 04	HW/FW neu: 05
2702499	;IB IL RTD 4/PT100-ECO;HW/FW alt: 03	HW/FW neu: 04
2702501	;IB IL RTD 4/PT1000-ECO;HW/FW alt: 03	HW/FW neu: 04
2702502	;IB IL UTH 4/J-ECO;HW/FW alt: 02	HW/FW neu: 03
2702503	;IB IL UTH 4/K-ECO;HW/FW alt: 02	HW/FW neu: 03
2702507	;IL EC BK-PAC;HW/FW alt: 06	HW/FW neu: 07
2702792	;IB IL 24 DI 8/HD-ECO;HW/FW alt: 04	HW/FW neu: 05
2702793	;IB IL 24 DO 8/HD-ECO;HW/FW alt: 01	HW/FW neu: 02
2702795	;IB IL RS 232-ECO;HW/FW alt: 01	HW/FW neu: 02
2702825	;IB IL 24 DO 4/EF-ECO;HW/FW alt: 01	HW/FW neu: 02
2703981	;IL ETH BK DI8 DO4 2TX-PAC;HW/FW alt: 24	HW/FW neu: 25
2703994	;IL PN BK DI8 DO4 2TX-PAC;HW/FW alt: 26	HW/FW neu: 27
2736903	;IB IL 24 FLM-PAC;HW/FW alt: 06	HW/FW neu: 07
2819574	;IB IL SSI-IN-PAC;HW/FW alt: 09	HW/FW neu: 10
2819765	;IB IL INC-IN-2MBD-PAC;HW/FW alt: 08	HW/FW neu: 09
2861205	;IB IL 24 MUX MA-PAC;HW/FW alt: 10	HW/FW neu: 11
2861218	;IBS IL 24 BK-LK-PAC;HW/FW alt: 11	HW/FW neu: 12
2861221	;IB IL 24 DI 2-PAC;HW/FW alt: 08	HW/FW neu: 09
2861234	;IB IL 24 DI 4-PAC;HW/FW alt: 14	HW/FW neu: 15
2861247	;IB IL 24 DI 8-PAC;HW/FW alt: 13	HW/FW neu: 14
2861250	;IB IL 24 DI 16-PAC;HW/FW alt: 12	HW/FW neu: 13
2861263	;IB IL 24 DO 2-2A-PAC;HW/FW alt: 12	HW/FW neu: 13
2861276	;IB IL 24 DO 4-PAC;HW/FW alt: 13	HW/FW neu: 14
2861289	;IB IL 24 DO 8-PAC;HW/FW alt: 13	HW/FW neu: 14

2861292	;IB IL 24 DO 16-PAC;HW/FW alt: 14	HW/FW neu: 15
2861302	;IB IL AI 2/SF-PAC;HW/FW alt: 12	HW/FW neu: 13
2861315	;IB IL AO 1/SF-PAC;HW/FW alt: 20	HW/FW neu: 21
2861328	;IB IL TEMP 2 RTD-PAC;HW/FW alt: 11	HW/FW neu: 12
2861331	;IB IL 24 PWR IN-PAC;HW/FW alt: 12	HW/FW neu: 09
2861344	;IB IL 24 SEG-PAC;HW/FW alt: 08	HW/FW neu: 06
2861357	;IB IL RS 232-PAC;HW/FW alt: 05	HW/FW neu: 06
2861360	;IB IL 24 TC-PAC;HW/FW alt: 05	HW/FW neu: 06
2861373	;IB IL 24 SEG/F-PAC;HW/FW alt: 09	HW/FW neu: 10
2861386	;IB IL TEMP 2 UTH-PAC;HW/FW alt: 11	HW/FW neu: 12
2861399	;IB IL AO 1/U/SF-PAC;HW/FW alt: 10	HW/FW neu: 11
2861409	;IB IL 24 SEG-ELF-PAC;HW/FW alt: 06	HW/FW neu: 07
2861412	;IB IL AI 8/SF-PAC;HW/FW alt: 11	HW/FW neu: 12
2861438	;IB IL 24 PWR IN/F-PAC;HW/FW alt: 06	HW/FW neu: 07
2861441	;IBS IL 24 RB-T-PAC;HW/FW alt: 08	HW/FW neu: 09
2861467	;IB IL AO 2/U/BP-PAC;HW/FW alt: 10	HW/FW neu: 11
2861506	;IBS IL 24 BK RB-LK-PAC;HW/FW alt: 07	HW/FW neu: 08
2863119	;IB IL 24/48 DOR 2/W-PAC;HW/FW alt: 05	HW/FW neu: 06
2863135	;IB IL 24 PWR IN/PS-PAC;HW/FW alt: 05	HW/FW neu: 06
2863520	;IB IL 24 DI 16-NPN-PAC;HW/FW alt: 10	HW/FW neu: 11
2863627	;IB IL RS 485/422-PRO-PAC;HW/FW alt: 12	HW/FW neu: 13
2863834	;IB IL 24 PWR IN/2F-DF-2MBD-PAC;HW/FW alt: 03	HW/FW neu: 04
2863915	;IB IL TEMP 4/8 RTD-PAC;HW/FW alt: 08	HW/FW neu: 09
2863928	;IB IL 24 DI 4-ME;HW/FW alt: 09	HW/FW neu: 10
2863931	;IB IL 24 DO 4-ME;HW/FW alt: 08	HW/FW neu: 09
2863944	;IB IL AI 2/SF-ME;HW/FW alt: 07	HW/FW neu: 08
2863957	;IB IL AO 2/U/BP-ME;HW/FW alt: 06	HW/FW neu: 07
2878036	;IB IL AO 4/8/U/BP-PAC;HW/FW alt: 05	HW/FW neu: 06
2878052	;IB IL AO 4/8/U/BP-2MBD-PAC;HW/FW alt: 05	HW/FW neu: 06
2878159	;IBS IL 24 RB-LK-2MBD;HW/FW alt: 02	HW/FW neu: 03
2878243	;IB IL 24 DI 32/HD-NPN-PAC;HW/FW alt: 09	HW/FW neu: 10
2878340	;IB IL 24 DO 32/HD-NPN-PAC;HW/FW alt: 09	HW/FW neu: 10
2878447	;IB IL AI 4/EF-PAC;HW/FW alt: 11	HW/FW neu: 12
2878638	;IB IL SGI 2/F-PAC;HW/FW alt: 10	HW/FW neu: 11
2878641	;IB IL AI 4/EF-2MBD-PAC;HW/FW alt: 07	HW/FW neu: 08
2878696	;IL MOD BK DI8 DO4-PAC;HW/FW alt: 22	HW/FW neu: 23
2878722	;IB IL RS 232-PRO-PAC;HW/FW alt: 11	HW/FW neu: 12
2878735	;IB IL SGI 2/F-2MBD-PAC;HW/FW alt: 08	HW/FW neu: 09
2884622	;IB IL TEMP 2 RTD-PAC/10;HW/FW alt: 04	HW/FW neu: 05
2897046	;IB IL CNT-PAC/10;HW/FW alt: 07	HW/FW neu: 07
2897143	;IB IL RS 485/422-PRO-PAC/10;HW/FW alt: 08	HW/FW neu: 08
2897156	;IB IL 24 DI 16-ME;HW/FW alt: 03	HW/FW neu: 04
2897240	;IBS IL 24 BK-LK-PAC/10;HW/FW alt: 07	HW/FW neu: 08
2861577	;IB IL AI 2/SF-230-PAC;HW/FW alt: 04	HW/FW neu: 05
2861580	;IBS IL 24 BK-T/U-PAC;HW/FW alt: 13	HW/FW neu: 14
2861593	;IBS IL 24 BK-DSUB-PAC;HW/FW alt: 11	HW/FW neu: 12
2861603	;IB IL 24 DO 8-2A-PAC;HW/FW alt: 07	HW/FW neu: 08
2861632	;IB IL PWM/2-PAC;HW/FW alt: 07	HW/FW neu: 08

2861661	;IB IL AI 8/IS-PAC;HW/FW alt: 06	HW/FW neu: 07
2861674	;IB IL 24 PWR IN/R-PAC;HW/FW alt: 11	HW/FW neu: 12
2861687	;IB IL 24 DO 8-2MBD-PAC;HW/FW alt: 09	HW/FW neu: 10
2861690	;IB IL 24 DI 8-2MBD-PAC;HW/FW alt: 06	HW/FW neu: 07
2861700	;IB IL 24 DO 2-2A-2MBD-PAC;HW/FW alt: 08	HW/FW neu: 09
2861755	;IB IL INC-IN-PAC;HW/FW alt: 11	HW/FW neu: 12
2861768	;IB IL IMPULSE-IN-PAC;HW/FW alt: 07	HW/FW neu: 08
2861852	;IB IL CNT-PAC;HW/FW alt: 08	HW/FW neu: 09
2861865	;IB IL SSI-PAC;HW/FW alt: 05	HW/FW neu: 06
2861904	;IB IL 24 SEG/F-D-PAC;HW/FW alt: 08	HW/FW neu: 09
2861933	;IB IL RS 485/422-PAC;HW/FW alt: 06	HW/FW neu: 07
2861959	;IB IL 24 DI16-2MBD-PAC;HW/FW alt: 06	HW/FW neu: 07
2861962	;IBS IL 24 RB-T-2MBD-PAC;HW/FW alt: 07	HW/FW neu: 08
2861988	;IB IL 24 DO 4-2MBD-PAC;HW/FW alt: 06	HW/FW neu: 07
2862000	;IBS IL 24 BK-T/U-2MBD-PAC;HW/FW alt: 09	HW/FW neu: 10
2862013	;IB IL 24 DO16-2MBD-PAC;HW/FW alt: 06	HW/FW neu: 07
2862068	;IBS IL 24 BK-LK-2MBD-PAC;HW/FW alt: 08	HW/FW neu: 09
2862084	;IB IL RS 232-2MBD-PAC;HW/FW alt: 05	HW/FW neu: 06
2862097	;IB IL RS 485/422-2MBD-PAC;HW/FW alt: 07	HW/FW neu: 08
2862136	;IB IL 24 PWR IN/2-F-PAC;HW/FW alt: 05	HW/FW neu: 06
2862152	;IB IL 24 PWR IN/2-F-D-PAC;HW/FW alt: 08	HW/FW neu: 09
2862194	;IB IL AO 2/SF-2MBD-PAC;HW/FW alt: 07	HW/FW neu: 08
2862204	;IB IL 24 DI 8/T2-PAC;HW/FW alt: 11	HW/FW neu: 12
2862217	;IB IL AI 2/4-20-PAC;HW/FW alt: 05	HW/FW neu: 06
2862246	;IL PB BK DP/V1-PAC;HW/FW alt: 16	HW/FW neu: 17
2862822	;IB IL 24 DO 32/HD-PAC;HW/FW alt: 14	HW/FW neu: 15
2862835	;IB IL 24 DI 32/HD-PAC;HW/FW alt: 14	HW/FW neu: 15
2862958	;IB IL 24 DI 16-PAC/SN;HW/FW alt: 10	HW/FW neu: 11
2862961	;IB IL 24 DO 16-PAC/SN;HW/FW alt: 11	HW/FW neu: 12
2862987	;IB IL PD 24V-PAC;HW/FW alt: 04	HW/FW neu: 05
2862990	;IB IL PD GND-PAC;HW/FW alt: 04	HW/FW neu: 05
2863083	;IB IL AO 2/SF-PAC;HW/FW alt: 08	HW/FW neu: 09

eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242605
eCl@ss 13.0: 27242605
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242601

eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242605
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242605
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242692
eCl@ss 13.0: 27242692
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242604

[illegible]

eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242605
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242605

eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242605
eCl@ss 13.0: 27242605
eCl@ss 13.0: 27242605
eCl@ss 13.0: 27242605
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242610
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242601
eCl@ss 13.0: 27242608
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242604
eCl@ss 13.0: 27242692
eCl@ss 13.0: 27242692
eCl@ss 13.0: 27242601

Kunde;Name 1;Name 2;Name 3;Name 4;Straße;PLZ;Stadt;Phoenix Contact Art.Nr.;Phoenix Contact Art.Bez.;Ihre |
49786 ;TTI
49786 ;TTI
49786 ;TTI
49786 ;TTI
49786 ;TTI

Materialnr.;	Menge 2024 ST;	Menge 2025 ST;	Menge 2026 ST;	AE 2026 ST
Inc.;;;Ganghoferstraße 34;82216;Maisach;2700459				;IB IL AI 4/U-PAC;;2 ST;;
Inc.;;;Ganghoferstraße 34;82216;Maisach;2861234				;IB IL 24 DI 4-PAC;;4 ST;;
Inc.;;;Ganghoferstraße 34;82216;Maisach;2861276				;IB IL 24 DO 4-PAC;;4 ST;;
Inc.;;;Ganghoferstraße 34;82216;Maisach;2702498				;IB IL AO 4/U/0-10-ECO;;2 ST;;
Inc.;;;Ganghoferstraße 34;82216;Maisach;2703981				;IL ETH BK DI8 DO4 2TX-PAC;;1 ST;;

Item no.;Type;old;new;Substitute item;Replacement product designation;eCl@ss 13.0;

2692306;IB IL 24 DI 4-2MBD-PAC;08;09;;;27242604;
2692720;IB IL IFS-MA-PAC;08;09;;;27242608;
2692885;IB IL 24 DI 32/HD-2MBD-PAC;10;11;;;27242604;
2692898;IB IL 24 DO 32/HD-2MBD-PAC;10;11;;;27242604;
2693020;IB IL 24 PWR IN/R/L-0.8A-PAC;10;11;;;27242610;
2700172;IB IL 24 DO8/HD-PAC;11;12;;;27242604;
2700196;IB IL CAN-MA-PAC;06;07;;;27242608;
2700458;IB IL AI 4/I-PAC;09;10;;;27242601;
2700459;IB IL AI 4/U-PAC;08;09;;;27242601;
2701000;IB IL TEMP 8 UTH/RTD-PAC;02;03;;;27242601;
2701009;IB IL 24 DO 4/EF-PAC;04;05;;;27242604;
2701480;IB IL 48 DI8/HD-PAC;02;03;;;27242604;
2702141;IB IL RS 485-ECO;03;04;;;27242608;
2702373;IB IL SGI 2/P/EF-PAC;03;04;;;27242601;
2702502;IB IL UTH 4/J-ECO;03;04;;;27242601;
2702503;IB IL UTH 4/K-ECO;03;04;;;27242601;
2702825;IB IL 24 DO 4/EF-ECO;02;03;;;27242604;
2736903;IB IL 24 FLM-PAC;07;08;;;27242608;
2819574;IB IL SSI-IN-PAC;10;11;;;27242605;
2819765;IB IL INC-IN-2MBD-PAC;09;10;;;27242605;
2861205;IB IL 24 MUX MA-PAC;11;12;;;27242608;
2861221;IB IL 24 DI 2-PAC;09;10;;;27242604;
2861234;IB IL 24 DI 4-PAC;15;16;;;27242604;
2861247;IB IL 24 DI 8-PAC;14;15;;;27242604;
2861250;IB IL 24 DI 16-PAC;13;14;;;27242604;
2861263;IB IL 24 DO 2-2A-PAC;13;14;;;27242604;
2861276;IB IL 24 DO 4-PAC;14;15;;;27242604;
2861289;IB IL 24 DO 8-PAC;14;15;;;27242604;
2861292;IB IL 24 DO 16-PAC;15;16;;;27242604;
2861315;IB IL AO 1/SF-PAC;21;22;;;27242601;
2861328;IB IL TEMP 2 RTD-PAC;12;13;;;27242601;
2861331;IB IL 24 PWR IN-PAC;13;14;;;27242610;
2861344;IB IL 24 SEG-PAC;09;10;;;27242610;
2861357;IB IL RS 232-PAC;07;08;;;27242608;
2861360;IB IL 24 TC-PAC;06;07;;;27242601;
2861373;IB IL 24 SEG/F-PAC;10;11;;;27242610;
2861386;IB IL TEMP 2 UTH-PAC;12;13;;;27242601;
2861399;IB IL AO 1/U/SF-PAC;11;12;;;27242601;
2861409;IB IL 24 SEG-ELF-PAC;07;08;;;27242610;
2861438;IB IL 24 PWR IN/F-PAC;07;08;;;27242610;
2861441;IB IL 24 RB-T-PAC;09;10;;;27242608;
2861467;IB IL AO 2/U/BP-PAC;11;12;;;27242601;
2861603;IB IL 24 DO 8-2A-PAC;08;09;;;27242604;
2861632;IB IL PWM/2-PAC;09;10;;;27242605;
2861687;IB IL 24 DO 8-2MBD-PAC;11;12;;;27242604;
2861690;IB IL 24 DI 8-2MBD-PAC;08;09;;;27242604;
2861700;IB IL 24 DO 2-2A-2MBD-PAC;09;10;;;27242604;

2861852;IB IL CNT-PAC;09;10;;;27242605;
2861904;IB IL 24 SEG/F-D-PAC;09;10;;;27242610;
2861933;IB IL RS 485/422-PAC;08;09;;;27242608;
2861959;IB IL 24 DI16-2MBD-PAC;07;08;;;27242604;
2861962;IBS IL 24 RB-T-2MBD-PAC;08;09;;;27242608;
2861988;IB IL 24 DO 4-2MBD-PAC;07;08;;;27242604;
2862084;IB IL RS 232-2MBD-PAC;07;08;;;27242608;
2862097;IB IL RS 485/422-2MBD-PAC;08;09;;;27242608;
2862152;IB IL 24 PWR IN/2-F-D-PAC;09;10;;;27242610;
2862204;IB IL 24 DI 8/T2-PAC;12;13;;;27242604;
2862822;IB IL 24 DO 32/HD-PAC;15;16;;;27242604;
2862835;IB IL 24 DI 32/HD-PAC;15;16;;;27242604;
2862958;IB IL 24 DI 16-PAC/SN;11;12;;;27242604;
2862987;IB IL PD 24V-PAC;06;07;;;27242692;
2862990;IB IL PD GND-PAC;06;07;;;27242692;
2863119;IB IL 24/48 DOR 2/W-PAC;08;09;;;27242604;
2863520;IB IL 24 DI 16-NPN-PAC;11;12;;;27242604;
2863627;IB IL RS 485/422-PRO-PAC;13;14;;;27242608;
2863834;IB IL 24 PWR IN/2F-DF-2MBD-PAC;04;05;;;27242610;
2863928;IB IL 24 DI 4-ME;10;11;;;27242604;
2863931;IB IL 24 DO 4-ME;09;10;;;27242604;
2863957;IB IL AO 2/U/BP-ME;07;08;;;27242601;
2878036;IB IL AO 4/8/U/BP-PAC;06;07;;;27242601;
2878052;IB IL AO 4/8/U/BP-2MBD-PAC;06;07;;;27242601;
2878159;IBS IL 24 RB-LK-2MBD;03;04;;;27242608;
2878243;IB IL 24 DI 32/HD-NPN-PAC;10;11;;;27242604;
2878340;IB IL 24 DO 32/HD-NPN-PAC;10;11;;;27242604;
2878722;IB IL RS 232-PRO-PAC;12;13;;;27242608;
2897156;IB IL 24 DI 16-ME;04;05;;;27242604;
2897253;IB IL 24 DO 16-ME;07;08;;;27242604;
2897402;IB IL TEMP 4/8 RTD/EF-PAC;15;16;;;27242601;
1185434;IB IL RTD 4/NTC-ECO;00;01;;;27242601;
2403696;IL PN BK-PAC;10;11;;;27242608;
2692306;IB IL 24 DI 4-2MBD-PAC;07;08;;;27242604;
2692322;IL PB BK DI8 DO4/EF-PAC;14;15;;;27242608;
2692380;IL S3 BK DI8 DO4 2TX-PAC;21;22;;;27242608;
2692720;IB IL IFS-MA-PAC;07;08;;;27242608;
2692885;IB IL 24 DI 32/HD-2MBD-PAC;09;10;;;27242604;
2692898;IB IL 24 DO 32/HD-2MBD-PAC;09;10;;;27242604;
2693020;IB IL 24 PWR IN/R/L-0.8A-PAC;09;10;;;27242610;
2700172;IB IL 24 DO8/HD-PAC;09;10;;;27242604;
2700173;IB IL 24 DI8/HD-PAC;14;15;;;27242604;
2700196;IB IL CAN-MA-PAC;04;05;;;27242608;
2700458;IB IL AI 4/I-PAC;07;08;;;27242601;
2700459;IB IL AI 4/U-PAC;07;08;;;27242601;
2700775;IB IL AO 2/UI-PAC;06;07;;;27242601;
2700893;IB IL RS UNI-PAC;10;11;;;27242608;
2701000;IB IL TEMP 8 UTH/RTD-PAC;01;02;;;27242601;

2701009;IB IL 24 DO 4/EF-PAC;03;03;;;27242604;
2701025;IB IL RS UNI-2MBD-PAC;06;07;;;27242608;
2701480;IB IL 48 DI8/HD-PAC;01;02;;;27242604;
2702141;IB IL RS 485-ECO;02;03;;;27242608;
2702230;IL CO BK-PAC;08;09;;;27242608;
2702372;IL ETH BK-PAC;04;05;;;27242608;
2702373;IB IL SGI 2/P/EF-PAC;02;03;;;27242601;
2702495;IB IL AI 4/I/4-20-ECO;04;05;;;27242601;
2702496;IB IL AI 4/U/0-10-ECO;04;05;;;27242601;
2702497;IB IL AO 4/I/4-20-ECO;05;06;;;27242601;
2702498;IB IL AO 4/U/0-10-ECO;04;05;;;27242601;
2702499;IB IL RTD 4/PT100-ECO;03;04;;;27242601;
2702501;IB IL RTD 4/PT1000-ECO;03;04;;;27242601;
2702502;IB IL UTH 4/J-ECO;02;03;;;27242601;
2702503;IB IL UTH 4/K-ECO;02;03;;;27242601;
2702507;IL EC BK-PAC;06;07;;;27242608;
2702792;IB IL 24 DI 8/HD-ECO;04;05;;;27242604;
2702793;IB IL 24 DO 8/HD-ECO;01;02;;;27242604;
2702795;IB IL RS 232-ECO;01;02;;;27242608;
2702825;IB IL 24 DO 4/EF-ECO;01;02;;;27242604;
2703981;IL ETH BK DI8 DO4 2TX-PAC;24;25;;;27242608;
2703994;IL PN BK DI8 DO4 2TX-PAC;26;27;;;27242608;
2736903;IB IL 24 FLM-PAC;06;07;;;27242608;
2819574;IB IL SSI-IN-PAC;09;10;;;27242605;
2819765;IB IL INC-IN-2MBD-PAC;08;09;;;27242605;
2861205;IB IL 24 MUX MA-PAC;10;11;;;27242608;
2861218;IBS IL 24 BK-LK-PAC;11;12;;;27242608;
2861221;IB IL 24 DI 2-PAC;08;09;;;27242604;
2861234;IB IL 24 DI 4-PAC;14;15;;;27242604;
2861247;IB IL 24 DI 8-PAC;13;14;;;27242604;
2861250;IB IL 24 DI 16-PAC;12;13;;;27242604;
2861263;IB IL 24 DO 2-2A-PAC;12;13;;;27242604;
2861276;IB IL 24 DO 4-PAC;13;14;;;27242604;
2861289;IB IL 24 DO 8-PAC;13;14;;;27242604;
2861292;IB IL 24 DO 16-PAC;14;15;;;27242604;
2861302;IB IL AI 2/SF-PAC;12;13;;;27242601;
2861315;IB IL AO 1/SF-PAC;20;21;;;27242601;
2861328;IB IL TEMP 2 RTD-PAC;11;12;;;27242601;
2861331;IB IL 24 PWR IN-PAC;12;09;;;27242610;
2861344;IB IL 24 SEG-PAC;08;06;;;27242610;
2861357;IB IL RS 232-PAC;05;06;;;27242608;
2861360;IB IL 24 TC-PAC;05;06;;;27242601;
2861373;IB IL 24 SEG/F-PAC;09;10;;;27242610;
2861386;IB IL TEMP 2 UTH-PAC;11;12;;;27242601;
2861399;IB IL AO 1/U/SF-PAC;10;11;;;27242601;
2861409;IB IL 24 SEG-ELF-PAC;06;07;;;27242610;
2861412;IB IL AI 8/SF-PAC;11;12;;;27242601;
2861438;IB IL 24 PWR IN/F-PAC;06;07;;;27242610;

2861441;IBS IL 24 RB-T-PAC;08;09;;;27242608;
2861467;IB IL AO 2/U/BP-PAC;10;11;;;27242601;
2861506;IBS IL 24 BK RB-LK-PAC;07;08;;;27242608;
2861577;IB IL AI 2/SF-230-PAC;04;05;;;27242601;
2861580;IBS IL 24 BK-T/U-PAC;13;14;;;27242608;
2861593;IBS IL 24 BK-DSUB-PAC;11;12;;;27242608;
2861603;IB IL 24 DO 8-2A-PAC;07;08;;;27242604;
2861632;IB IL PWM/2-PAC;07;08;;;27242605;
2861661;IB IL AI 8/IS-PAC;06;07;;;27242601;
2861674;IB IL 24 PWR IN/R-PAC;11;12;;;27242610;
2861687;IB IL 24 DO 8-2MBD-PAC;09;10;;;27242604;
2861690;IB IL 24 DI 8-2MBD-PAC;06;07;;;27242604;
2861700;IB IL 24 DO 2-2A-2MBD-PAC;08;09;;;27242604;
2861755;IB IL INC-IN-PAC;11;12;;;27242605;
2861768;IB IL IMPULSE-IN-PAC;07;08;;;27242605;
2861852;IB IL CNT-PAC;08;09;;;27242605;
2861865;IB IL SSI-PAC;05;06;;;27242605;
2861904;IB IL 24 SEG/F-D-PAC;08;09;;;27242610;
2861933;IB IL RS 485/422-PAC;06;07;;;27242608;
2861959;IB IL 24 DI16-2MBD-PAC;06;07;;;27242604;
2861962;IBS IL 24 RB-T-2MBD-PAC;07;08;;;27242608;
2861988;IB IL 24 DO 4-2MBD-PAC;06;07;;;27242604;
2862000;IBS IL 24 BK-T/U-2MBD-PAC;09;10;;;27242608;
2862013;IB IL 24 DO16-2MBD-PAC;06;07;;;27242604;
2862068;IBS IL 24 BK-LK-2MBD-PAC;08;09;;;27242608;
2862084;IB IL RS 232-2MBD-PAC;05;06;;;27242608;
2862097;IB IL RS 485/422-2MBD-PAC;07;08;;;27242608;
2862136;IB IL 24 PWR IN/2-F-PAC;05;06;;;27242610;
2862152;IB IL 24 PWR IN/2-F-D-PAC;08;09;;;27242610;
2862194;IB IL AO 2/SF-2MBD-PAC;07;08;;;27242601;
2862204;IB IL 24 DI 8/T2-PAC;11;12;;;27242604;
2862217;IB IL AI 2/4-20-PAC;05;06;;;27242601;
2862246;IL PB BK DP/V1-PAC;16;17;;;27242608;
2862822;IB IL 24 DO 32/HD-PAC;14;15;;;27242604;
2862835;IB IL 24 DI 32/HD-PAC;14;15;;;27242604;
2862958;IB IL 24 DI 16-PAC/SN;10;11;;;27242604;
2862961;IB IL 24 DO 16-PAC/SN;11;12;;;27242604;
2862987;IB IL PD 24V-PAC;04;05;;;27242692;
2862990;IB IL PD GND-PAC;04;05;;;27242692;
2863083;IB IL AO 2/SF-PAC;08;09;;;27242601;
2863119;IB IL 24/48 DOR 2/W-PAC;05;06;;;27242604;
2863135;IB IL 24 PWR IN/PS-PAC;05;06;;;27242610;
2863520;IB IL 24 DI 16-NPN-PAC;10;11;;;27242604;
2863627;IB IL RS 485/422-PRO-PAC;12;13;;;27242608;
2863834;IB IL 24 PWR IN/2F-DF-2MBD-PAC;03;04;;;27242610;
2863915;IB IL TEMP 4/8 RTD-PAC;08;09;;;27242601;
2863928;IB IL 24 DI 4-ME;09;10;;;27242604;
2863931;IB IL 24 DO 4-ME;08;09;;;27242604;

2863944;IB IL AI 2/SF-ME;07;08;;;27242601;
2863957;IB IL AO 2/U/BP-ME;06;07;;;27242601;
2878036;IB IL AO 4/8/U/BP-PAC;05;06;;;27242601;
2878052;IB IL AO 4/8/U/BP-2MBD-PAC;05;06;;;27242601;
2878159;IBS IL 24 RB-LK-2MBD;02;03;;;27242608;
2878243;IB IL 24 DI 32/HD-NPN-PAC;09;10;;;27242604;
2878340;IB IL 24 DO 32/HD-NPN-PAC;09;10;;;27242604;
2878447;IB IL AI 4/EF-PAC;11;12;;;27242601;
2878638;IB IL SGI 2/F-PAC;10;11;;;27242601;
2878641;IB IL AI 4/EF-2MBD-PAC;07;08;;;27242601;
2878696;IL MOD BK DI8 DO4-PAC;22;23;;;27242608;
2878722;IB IL RS 232-PRO-PAC;11;12;;;27242608;
2878735;IB IL SGI 2/F-2MBD-PAC;08;09;;;27242601;
2884622;IB IL TEMP 2 RTD-PAC/10;04;05;;;27242601;
2897046;IB IL CNT-PAC/10;07;07;;;27242605;
2897143;IB IL RS 485/422-PRO-PAC/10;08;08;;;27242608;
2897156;IB IL 24 DI 16-ME;03;04;;;27242604;
2897240;IBS IL 24 BK-LK-PAC/10;07;08;;;27242608;
2897253;IB IL 24 DO 16-ME;05;06;;;27242604;
2897334;IB IL 24 DI 2-PAC/10;04;05;;;27242604;
2897347;IBS IL 24 BK-DSUB-PAC/10;06;07;;;27242608;
2897402;IB IL TEMP 4/8 RTD/EF-PAC;14;15;;;27242601;
2897431;IB IL 24 DI 8/T2-PAC/10;05;06;;;27242604;
2897444;IBS IL 24 RB-T-PAC/10;06;07;;;27242608;
2897457;IB IL 24 LSKIP-PAC;06;07;;;27242608;
2897538;IB IL 24 DO 16-PAC/10;05;06;;;27242604;
2897635;IB IL 24 PWR IN-PAC/10;04;05;;;27242610;
2897732;IB IL 24 SEG-ELF-PAC/10;03;04;;;27242610;
2897758;IL EIP BK DI8 DO4 2TX-PAC;18;19;;;27242608;
2897839;IB IL AI 2/SF-PAC/10;05;06;;;27242601;
2897936;IB IL AO 2/U/BP-PAC/10;04;05;;;27242601;
2897952;IB IL AI/TEMP 4 RTD-PAC;02;03;;;27242601;

